


Rittal – The System.

Faster – better – everywhere.



DK 7824.188

Side panel, lockable

State: 8/4/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7824.188 - Side panel, lockable for TS, TS IT

Side panel, lockable, sheet steel, for TS.



Features

| | |
|-----------------------|--|
| Model No. | DK 7824.188 |
| Product description | Locates easily into place at the top. Locked with security lock no. 3524 E. Grounding bolts with contact lug. |
| Material | Carbon steel |
| Surface finish | Spray-finished |
| Color | RAL 7035 |
| Supply includes | 2 side panels each with 4 security locks no. 3524 E |
| Suitable for | Enclosure type: TS TS IT Height: 1,800 mm Depth: 800 mm Enclosure type: TS TS IT Height: 70.9 " Depth: 31.5 " |
| Base material | Carbon steel |
| Packaging unit | 2 pc(s). |
| Net weight | 34.4 |
| Gross weight | 35.8 |
| Customs tariff number | 94039910 |

Features

| | |
|-----------------|---------------|
| EAN | 4028177232037 |
| E-Number Sweden | E7282526 |
| ETIM 9 | EC002524 |
| ECLASS 8.0 | 27182101 |