


Rittal – The System.

Faster – better – everywhere.



DK 7825.375

Brush strip, super-airtight

State: 7/13/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7825.375 - Brush strip, super-airtight

These special brush strips can be used to create airtight entries for cable bundles and conductors.

Features

Model No.	DK 7825.375
Product description	For individual installation of enclosure panels, gland plates and panels. Cut-outs for cable routing at any position in the side panel, rear panel, doors, roof and base plate. These special brush strips may be used to create airtight entries for cable sections and conductors. The brush strips arranged in an offset configuration ensure good sealing from the routed cables even with large quantities of cables. In this way, unwanted flow losses may be reduced to a minimum.
Material	Brush strip: Plastic, UL 94-HB
Supply includes	1 brush strip each, 1 m in length, right-hand and left-hand version
Bristle length	58 mm 2.28 "
Length	1 m 39.4 "
Dimensions	Length: 1 m Length: 39.4 "
For material thicknesses	1.5 - 2 mm 0.06 - 0.08 "
Packaging unit	1 pc(s).
Net weight	0.65
Gross weight	0.82
Customs tariff number	96035000
EAN	4028177552784
ETIM 9	EC002620
ECLASS 8.0	27189261