

Rittal – The System.

Faster – better – everywhere.



DK 7826.750

Vent cover

State: 4/8/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7826.750 - Vent cover for VX, VX IT

To connect sealed racks to the ventilation system. The stepped connection is suitable for standard duct diameters 150 mm and 200 mm, ensuring effective cooling as a result of targeted air exchange inside the rack.

Features

Model No.	DK 7826.750
Product description	The ideal addition for incorporating closed racks into an existing central climate control system. The stepped connection is suitable for standard conduit diameters, thereby ensuring effective cooling by means of targeted air exchange in the rack.
Material	PET-G
Color	Transparent
Supply includes	Assembly components
Ø Hose connection	150 mm 200 mm 5.91 " 7.87 "
Note	Cut-out required in roof plate (W x D): 380 x 230 mm
Dimensions	Width: 450 mm Height: 144 mm Depth: 300 mm Width: 17.7 " Height: 5.67 " Depth: 11.8 "
Packaging unit	1 pc(s).
Net weight	0.959 kg
Gross weight	0.96 kg
Customs tariff number	39269097
ETIM 9	EC000331
ECLASS 8.0	27189272

Features

Product description

DK vent cover, for hot air extraction to a ventilation system, WHD: 450 x 144 x 300 mm, cut-outs W x D max. 380 x 230 mm, PET-G, transparent