

Rittal – The System.

Faster – better – everywhere.



DK 7826.760

Roof Plate, Vented

State: 12/8/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7826.760 - Roof Plate, Vented for TS, TS IT

To replace the standard roof, with and without cable entry.



Features

Model No.	DK 7826.760
Version	One-piece without cable entry
Product description	To replace standard roof. 72 mm high roof plate, all-round vent slots, clamping profile for cable entry. The two-piece design with cable entry allows for easy retro-fitting.
Material	Carbon steel
Color	RAL 7035
Note on Model No.:	Delivery times on request.
Suitable for	Enclosure type: TS TS IT Width: 600 mm Depth: 1,000 mm Enclosure type: TS TS IT Width: 23.6 " Depth: 39.4 "
Packaging unit	1 pc(s).
Net weight	8.265
Gross weight	8.7
Customs tariff number	73269098
EAN	4028177345614

Features

ETIM 9	EC000744
ECLASS 8.0	27182405