

Rittal – The System.

Faster – better – everywhere.



DK 7827.100

Profile rails, 482.6 mm (19")

State: 5/23/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7827.100 - Profile rails, 482.6 mm (19") for TS, CS Toptec

Profile rails in right-angled version. Profile rails are alternately available as L-shaped profile rails.

Features

Model No.	DK 7827.100
Version	Cranked
Benefits	Integral U markings in the front facilitate systematic assembly within the 19" level.
Technical specifications	Integral 482.6 mm (19") punchings (EIA standard) Side round and square punchings Clear chromated for conductive connection of 19" fixtures
Material	Carbon steel, 2 mm
Supply includes	Assembly components
Dimensions	Width: 482.6 mm Width: 19 "
Height units	20 U
Note	The profile rails can also be used to accommodate 21", 23" and 24" attachment dimensions. Please select the slide rails according to the respective 19" plane spacing. For a combination with the L-shaped profile rails, the use of the mounting adapter for L-shaped profile rails is required.
Suitable for	Enclosure type: TS 8 CS Toptec Height: 1,000 mm Enclosure type: TS 8 CS Toptec Height: 39.4 "
Packaging unit	2 pc(s).
Net weight	2.844 kg

Features

Gross weight	3.043 kg
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261
