## Rittal – The System.

Faster – better – everywhere.





DK 7827.140

Profile rails, 482.6 mm (19")

State: 11/6/2025 (Source: rittal.com/us-en)



## DK 7827.140 - Profile rails, 482.6 mm (19") for TS, CS Toptec

Profile rails in right-angled version. Profile rails are alternately available as L-shaped profile rails.

## **Features**

Model No.	DK 7827.140
Version	Cranked
Benefits	Integral U markings in the front facilitate systematic assembly within the 19" level.
Technical specifications	Integral 482.6 mm (19") punchings (EIA standard)
	Side round and square punchings
	Clear chromated for conductive connection of 19" fixtures
Material	Carbon steel, 2 mm
Supply includes	Assembly components
Dimensions	Width: 482.6 mm
	Width: 19 "
Height units	29 U
Note	The profile rails can also be used to accommodate 21", 23" and 24" attachment dimensions.
	Please select the slide rails according to the respective 19" plane
	spacing.
	For a combination with the L-shaped profile rails, the use of the
	mounting adapter for L-shaped profile rails is required.
Suitable for	Enclosure type: TS 8
	CS Toptec
	Height: 1,400 mm
	Enclosure type: TS 8
	CS Toptec
	Height: 55.1 "
Packaging unit	2 pc(s).
Net weight	4.17

© Rittal 2025

## **Features**

Gross weight	4.34
Customs tariff number	73269098
EAN	4028177234871
ETIM 9	EC002620
ECLASS 8.0	27189261

© Rittal 2025 3