Rittal – The System.

Faster – better – everywhere.



DK 7827.180

Profile rails, 482.6 mm (19")

State: 11/15/2026 (Source: www.rittal.com/us-en)

DK 7827.180 - Profile rails, 482.6 mm (19") for TS, CS Toptec

Profile rails in right-angled version. Profile rails are alternately available as L-shaped profile rails.

Features

Model No.	DK 7827.180
Version	Cranked
Benefits	Integral U markings in the front facilitate systematic assembly within the 19" level.
Technical specifications	Integral 482.6 mm (19") punchings (EIA standard) Side round and square punchings Clear chromated for conductive connection of 19" fixtures
Material	Carbon steel, 2 mm
Supply includes	Assembly components
Dimensions	Width: 482.6 mm Width: 19 ″
Height units	38 U
Note	The profile rails can also be used to accommodate 21", 23" and 24" attachment dimensions. Please select the slide rails according to the respective 19" plane spacing. For a combination with the L-shaped profile rails, the use of the mounting adapter for L-shaped profile rails is required.
Suitable for	Enclosure type: TS 8 CS Toptec Height: 1,800 mm Enclosure type: TS 8 CS Toptec Height: 70.9 ″
Packaging unit	2 pc(s).
Net weight	5.266 kg

© Rittal 2026

Features

Gross weight	5.543 kg
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261

© Rittal 2026