

Rittal – The System.

Faster – better – everywhere.



DK 7827.181

Profile rails, 482.6 mm (19")

State: 4/26/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7827.181 - Profile rails, 482.6 mm (19") for TS

L profile rails, can also accommodate installation kits for server systems.

Features

| | |
|--------------------------|--|
| Model No. | DK 7827.181 |
| Version | L-shaped mounting angle |
| Benefits | Integral U markings in the front facilitate systematic assembly within the 19" level. L rails accommodate the installation kits of server systems Suitable for 19" partial expansion |
| Technical specifications | Integral 482.6 mm (19") punchings (EIA standard) Side round and square punchings Clear chromated for conductive connection of 19" fixtures |
| Material | Carbon steel, 2 mm |
| Supply includes | Assembly components |
| Height units | 38 U |
| Note | Please select the slide rails according to the respective 19" plane spacing. For a combination with the L-shaped profile rails, the use of the mounting adapter for L-shaped profile rails is required. |
| Suitable for | Enclosure type: TS Height: 1,800 mm Enclosure type: TS Height: 70.9 " |
| Packaging unit | 2 pc(s). |
| Net weight | 4.122 kg |
| Gross weight | 4.3 kg |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |

Features

Product description

DK-TS Mounting angles, 482.6 mm (19"), L-shaped mounting angle,
For H: 1800 mm, 38 U