

# Rittal – The System.

Faster – better – everywhere.



DK 7827.200

Profile rails, 482.6 mm (19")

State: 2/10/2026 (Source: [ittal.com/us-en](http://ittal.com/us-en))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# DK 7827.200 - Profile rails, 482.6 mm (19") for TS, CS Toptec

Profile rails in right-angled version. Profile rails are alternately available as L-shaped profile rails.

## Features

|                          |   |
|--------------------------|---|
| Model No.                | DK 7827.200   |
| Version                  | Cranked   |
| Benefits                 | Integral U markings in the front facilitate systematic assembly within the 19" level.   |
| Technical specifications | Integral 482.6 mm (19") punchings (EIA standard)<br>Side round and square punchings<br>Clear chromated for conductive connection of 19" fixtures  |
| Material                 | Carbon steel, 2 mm  |
| Supply includes          | Assembly components   |
| Dimensions               | Width: 482.6 mm<br>Width: 19 "  |
| Height units             | 42 U  |
| Note                     | The profile rails can also be used to accommodate 21", 23" and 24" attachment dimensions.<br>Please select the slide rails according to the respective 19" plane spacing.<br>For a combination with the L-shaped profile rails, the use of the mounting adapter for L-shaped profile rails is required. |
| Suitable for             | Enclosure type: TS 8<br>CS Toptec<br>Height: 2,000 mm<br>Enclosure type: TS 8<br>CS Toptec<br>Height: 78.7 "  |
| Packaging unit           | 2 pc(s).  |
| Net weight               | 5.842   |

# Features

---

|                       |               |
|-----------------------|---------------|
| Gross weight          | 6.26          |
| Customs tariff number | 73269098      |
| EAN                   | 4028177234932 |
| E-Number Sweden       | E7239688      |
| ETIM 9                | EC002620      |
| ECCLASS 8.0           | 27189261      |

---