

Rittal – The System.

Faster – better – everywhere.



DK 7827.221

Profile rails, 482.6 mm (19")

State: 5/13/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7827.221 - Profile rails, 482.6 mm (19") for TS

L profile rails, can also accommodate installation kits for server systems.

Features

Model No.	DK 7827.221
Version	L-shaped mounting angle
Benefits	Integral U markings in the front facilitate systematic assembly within the 19" level. L rails accommodate the installation kits of server systems Suitable for 19" partial expansion
Technical specifications	Integral 482.6 mm (19") punchings (EIA standard) Side round and square punchings Clear chromated for conductive connection of 19" fixtures
Material	Carbon steel, 2 mm
Supply includes	Assembly components
Height units	47 U
Note	Please select the slide rails according to the respective 19" plane spacing. For a combination with the L-shaped profile rails, the use of the mounting adapter for L-shaped profile rails is required.
Suitable for	Enclosure type: TS Height: 2,200 mm Enclosure type: TS Height: 86.6 "
Packaging unit	2 pc(s).
Net weight	4.958 kg
Gross weight	5.218 kg
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189261

Features

Product description

DK-TS Mounting angles, 482.6 mm (19"), L-shaped mounting angle,
For H: 2200 mm, 47 U