

Rittal – The System.

Faster – better – everywhere.



DK 7831.472

System supports for cable routes

State: 8/25/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7831.472 - System supports for cable routes for VX, VX IT

Depth-variable support system, allows for the attachment of most common cable route systems, may be attached to all 800 – 1200 mm deep network racks with external screw-fastening of the roof plate.



Features

| | |
|-----------------------|--|
| Model No. | DK 7831.472 |
| Version | Support height 102 mm |
| Product description | The depth-variable support system can be attached to all 800 – 1200 mm deep network racks with external screw fastening of the roof plate. Unique hole profile has been integrated for sheet metal screws or captive nuts to attach the most common cable routing systems. |
| Material | Carbon steel |
| Surface finish | Powder-coated |
| Color | RAL 7035 |
| Load capacity, static | 2,500 N |
| Note | May be combined with fan mounting plate for VX IT In combination with the punched rail, suitable for accommodating additional cable routing rails or pipelines. |
| Base material | Carbon steel |
| Packaging unit | 2 pc(s). |
| Net weight | 3.29 |

Features

| | |
|-------------------------------------|--|
| Gross weight | 3.49 |
| PCF/VE (cradle-to-gate) | 13.3 kg CO2 eq (Cat B) |
| Information regarding the PCF class | Category B: PCF value (cradle-to-gate) calculated approximately on the basis of the product weight and self-declared |
| Customs tariff number | 73269098 |
| EAN | 4028177517301 |
| ETIM 9 | EC000322 |
| ECLASS 8.0 | 27400604 |