

**Rittal – The System.**

Faster – better – everywhere.



**DK 7831.472**

**System supports for cable routes**

State: 5/11/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7831.472 - System supports for cable routes for VX, VX IT

Depth-variable support system, allows for the attachment of most common cable route systems, may be attached to all 800 – 1200 mm deep network racks with external screw-fastening of the roof plate.



## Features

Model No.	DK 7831.472
Version	Support height 102 mm
Product description	The depth-variable support system can be attached to all 800 – 1200 mm deep network racks with external screw fastening of the roof plate. Unique hole profile has been integrated for sheet metal screws or captive nuts to attach the most common cable routing systems.
Material	Carbon steel
Surface finish	Powder-coated
Color	RAL 7035
Load capacity, static	2,500 N
Note	May be combined with fan mounting plate for VX IT In combination with the punched rail, suitable for accommodating additional cable routing rails or pipelines.
Base material	Carbon steel
Packaging unit	2 pc(s).
Net weight	3.29

# Features

Gross weight	3.49
PCF per pack (cradle-to-gate)	13.3 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177517301
ETIM 9	EC000322
ECLASS 8.0	27400604