

Rittal – The System.

Faster – better – everywhere.



DK 7955.133

PDU international, basic version

State: 7/18/2025 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7955.133 - PDU international, basic version

IT rack power distributor in a range of designs. Input with CEE plug (16 A/32 A) and C13 and C19 outputs. Distribution output from 3.7 kW to 22 kW.

Features

Model No.	DK 7955.133
Version	PDU Basic
Product description	Robust, compact basic power distributor for the IT environment. Thanks to the compact PDU, all IT racks can easily be equipped with a professional power distribution system. In the case of the TS IT rack, mounting is even possible without tools. The compact design enables easy mounting.
Material	Aluminum section, black anodized
Dimensions	Width: 44 mm Depth: 62 mm Length: 1,365 mm Width: 1.73 " Depth: 2.44 " Length: 53.7 "
Number of sockets and type	24 x C13 / 6 x C19
Outlets	24 x Non-Heating Apparatus Socket C13 6 x Non-Heating Apparatus Socket C19
Rated current (max.)	32 A
Infeeds	Qty.: 1 Phases per infeed: 3~
Length of connection cable	3 m 118 "
Type of connection (electrical)	CEE
Number RJ45 ports for sensor units max	6
Guidelines	EMC Directive 2014/30/EU Low-Voltage Directive 2014/35/EU

Features

Standards	EN 60950-1
Operating temperature range	0 °C...45 °C 32 °F...113 °F
Ambient humidity (non-condensing)	10...95 %
Storage temperature range	-25 °C...70 °C -13 °F...158 °F
Suitable for	Enclosure type: TS IT: ≥ 1,800 mm Enclosure type: TS IT: ≥ 70.9 "
Packaging unit	1 pc(s).
Net weight	5.634
Gross weight	5.931
Customs tariff number	85366990
EAN	4028177684959
ECLASS 8.0	27142604