Rittal – The System.

Faster – better – everywhere.



SK 7980.000

Fan expansion kit

State: 11/12/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SK 7980.000 - Fan expansion kit

For retro-fitting various fan units or to expand the fan mounting plate

Features

Model No.	SK 7980.000
Product description	Can be used as a stand-alone fan and for retrofitting various fan units or to extend the fan mounting plate.
Supply includes	Fans Connection cable (0.61 m) Assembly components
Unimpeded air flow (with chopped fiber filter)	At 50 Hz: 160 m³/h At 60 Hz: 180 m³/h At 50 Hz: 94.2 cfm At 60 Hz: 105.9 cfm
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Rated power Pel	At 50 Hz: 15 W At 60 Hz: 14 W
Dimensions	Width: 119 mm Height: 119 mm Depth: 38 mm Width: 4.69 ″ Height: 4.69 ″ Depth: 1.5 ″
Operating temperature range	-10 °C...55 °C 14 °F...131 °F
Noise pressure level	At 50 Hz: 37 dB(A) At 60 Hz: 37 dB(A)
Packaging unit	1 pc(s).
Net weight	0.6 kg
Gross weight	0.671 kg
Customs tariff number	84145915

Features

ETIM 9	EC000320
ECLASS 8.0	27180716
Product description	DK Fan expansion kit, for use as a stand-alone fan, and for upgrading various fan units or to supplement the fan mounting plate, WxHxD: 119x119x38 mm, 230 V, 1 ~, 50/60 Hz