
Rittal – The System.

Faster – better – everywhere.



VX 8001.218
Gland plate

State: 11/12/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

VX 8001.218 - Gland plate for VX, VX IT, VX SE

For individual configuration of the floor space. Potential equalization is achieved via assembly components and earthing points.

Features

Model No.	VX 8001.218
Product description	For individual configuration of the floor space. Potential equalization is achieved via assembly components and earthing points.
Material	Carbon steel
Surface finish	Zinc-plated
Supply includes	Assembly components
Note	At least one sliding plate is required to fully seal a base opening. For two-door enclosures, one pack is sufficient for one half of the enclosure
Dimensions	Width: 490 mm Depth: 237.5 mm Width: 19.3 ″ Depth: 9.35 ″
Suitable for	Enclosure type: VX VX IT VX SE CX One-Piece Console CX Pedestal Width: = 600 mm Enclosure type: VX VX IT VX SE CX One-Piece Console CX Pedestal Width: = 23.6 ″
Packaging unit	1 pc(s).
Net weight	1.56 kg

Features

Gross weight	1.66 kg
Customs tariff number	94039910
ETIM 9	EC002620
ECLASS 8.0	27189261
Product description	VX Gland plate, WD: 600x237,5 mm

Approvals

Approvals	UL + C-UL (listed)