Rittal – The System.

Faster – better – everywhere.





WM 8017.530 WM wall-mounted enclosure

State: 11/29/2025 (Source: rittal.com/us-en)



WM 8017.530 - WM wall-mounted enclosure single-door

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.

Features

Model No.	WM 8017.530
Material	Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with door(s) Door hinged on left Mounting plate Rear wall mounting holes Quarter turn latch with slotted head insert
Dimensions	Width: 400 mm Height: 400 mm Depth: 150 mm Width: 15.7 " Height: 15.7 " Depth: 5.91 "
Dimensions of mounting plate (W x H)	354 mm x 375 mm 13.9 ″ x 14.8 ″
Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 12
Material thickness - door	1.5 mm 0.06 ″

© Rittal 2025 2

Features

Material thickness - enclosure	1.5 mm
	0.06 ″
Material thickness - mounting	1.5 mm
plate	0.06 ″
Packaging unit	1 pc(s).
Net weight	17.637
Gross weight	19.195
Customs tariff number	7326908688
UPC-Code	83117

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3