Rittal – The System.

Faster – better – everywhere.






WM 8017.532 WM wall-mounted enclosure

State: 11/29/2025 (Source: rittal.com/us-en)



WM 8017.532 - WM wall-mounted enclosure single-door

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.



Features

Model No.	WM 8017.532
Material	Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside,
	textured paint
	Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with door(s)
	Door hinged on left
	Mounting plate
	Rear wall mounting holes
	Quarter turn latch with slotted head insert
Dimensions	Width: 400 mm
	Height: 500 mm
	Depth: 150 mm
	Width: 15.7 "
	Height: 19.7 "
	Depth: 5.91 "
Dimensions of mounting plate (W	360 mm x 475 mm
x H)	14.2 ″ x 18.7 ″

© Rittal 2025 2

Features

NEMA 1
NEMA 3R
NEMA 4
NEMA 12
1.5 mm
0.06 ″
1.5 mm
0.06 ″
1.5 mm
0.06 ″
1 pc(s).
30
30.864
7326908688
83119

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3