Rittal - The System.

Faster – better – everywhere.





WM 8017.534 WM wall-mounted enclosure

State: 11/15/2025 (Source: rittal.com/us-en)



WM 8017.534 - WM wall-mounted enclosure single-door

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.







Features

Model No.	WM 8017.534
Material	Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint
	Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with door(s)
	Door hinged on left
	Mounting plate
	Rear wall mounting holes
	Quarter turn latch with slotted head insert
Dimensions	Width: 400 mm
	Height: 600 mm
	Depth: 150 mm
	Width: 15.7 "
	Height: 23.6 "
	Depth: 5.91 ″
Dimensions of mounting plate (W	354 mm x 570 mm
x H)	13.9 ″ x 22.4 ″

© Rittal 2025 2

Features

Protection category NEMA	NEMA 1
	NEMA 3R
	NEMA 4
	NEMA 12
Material thickness - door	1.5 mm
	0.06 ″
Material thickness - enclosure	1.5 mm
	0.06 ″
Material thickness – mounting	2.5 mm
plate	0.1 ″
Packaging unit	1 pc(s).
Net weight	35
Gross weight	35.273
Customs tariff number	7326909099
UPC-Code	83121

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3