



WM 8017.554 - WM wall-mounted enclosure single-door

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.



Features

| | |
|--------------------------------------|--|
| Model No. | WM 8017.554 |
| Material | Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel |
| Surface finish | Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated |
| Color | RAL 7035 |
| Supply includes | Housing with door(s) Door hinged on left Mounting plate Rear wall mounting holes Quarter turn latch with slotted head insert |
| Dimensions | Width: 600 mm Height: 900 mm Depth: 210 mm Width: 23.6 " Height: 35.4 " Depth: 8.27 " |
| Dimensions of mounting plate (W x H) | 549 mm x 870 mm 21.6 " x 34.3 " |

Features

| | |
|-------------------------------------|--|
| Protection category NEMA | NEMA 1 NEMA 3R NEMA 4 NEMA 12 |
| Material thickness - door | 2 mm 0.08 " |
| Material thickness - enclosure | 1.5 mm 0.06 " |
| Material thickness – mounting plate | 2.5 mm 0.1 " |
| Packaging unit | 1 pc(s). |
| Net weight | 70.547 lb |
| Gross weight | 73.854 lb |
| Customs tariff number | 8538100000 |

Approvals

| | |
|--------------|---------------------------|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |
