Rittal – The System.

Faster – better – everywhere.



# WM 8017.571

# WM wall-mounted enclosure

State: 11/11/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# WM 8017.571 - WM wall-mounted enclosure single-door

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.



## Features

| | |
|---|---|
| Model No. | WM 8017.571 |
| Material | Door: Carbon steel, all-round foamed-in PU seal<br>Housing: Carbon steel |
| Surface finish | Housing and door: Dipcoat primed, powder-coated on the outside, textured paint<br>Mounting panel: Zinc-plated |
| Color | RAL 7035 |
| Supply includes | Housing with door(s)<br>Door hinged on left<br>Mounting plate<br>Rear wall mounting holes<br>3-point latching L-Handle |
| Dimensions | Width: 900 mm<br>Height: 1,500 mm<br>Depth: 250 mm<br>Width: 35.4 ″<br>Height: 59.1 ″<br>Depth: 9.84 ″ |
| Dimensions of mounting plate (W x H) | 840 mm x 1,455 mm<br>33.1 ″ x 57.3 ″ |

© Rittal 2026

# Features

| | |
|---|---|
| Protection category NEMA | NEMA 1<br>NEMA 3R<br>NEMA 4<br>NEMA 12 |
| Material thickness - door | 2 mm<br>0.08 ″ |
| Material thickness - enclosure | 2 mm<br>0.08 ″ |
| Material thickness – mounting plate | 2.5 mm<br>0.1 ″ |
| 3-point locking system | Yes |
| Packaging unit | 1 pc(s). |
| Net weight | 198.413 lb |
| Gross weight | 200.254 lb |
| Customs tariff number | 8538100000 |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |