## Rittal – The System.

Faster – better – everywhere.





# WM 8017.588 WM wall-mounted enclosure

State: 11/14/2025 (Source: rittal.com/us-en)



## WM 8017.588 - WM wall-mounted enclosure single-door

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.



#### **Features**

Model No.	WM 8017.588
Material	Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with door(s) Door hinged on left Mounting plate Rear wall mounting holes 3-point latching L-Handle
Dimensions	Width: 900 mm Height: 1,200 mm Depth: 300 mm Width: 35.4 " Height: 47.2 " Depth: 11.8 "
Dimensions of mounting plate (W x H)	840 mm x 1,155 mm 33.1 " x 45.5 "

© Rittal 2025 2

## Features

NEMA 1
NEMA 3R
NEMA 4
NEMA 12
2 mm
0.08 ″
2 mm
0.08 ″
2.5 mm
0.1 ″
Yes
1 pc(s).
167.795
189.594
7326909099
83165

## **Approvals**

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3