

# Rittal – The System.

Faster – better – everywhere.



## WM 8017.603

## WM wall-mounted enclosure

State: 5/26/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# WM 8017.603 - WM wall-mounted enclosure 304 stainless steel

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a stainless steel body and door, and a zinc plated mounting panel.

## Features

|                                      |  |
|--------------------------------------|--|
| Model No.                            | WM 8017.603  |
| Material                             | Door: Stainless steel, all-round foamed-in PU seal<br>Housing and door: Stainless steel 1.4301 (AISI 304)<br>Mounting plate: Carbon steel, zinc-plated |
| Surface finish                       | Brushed  |
| Supply includes                      | Housing with door(s)<br>Door hinged on left<br>Mounting plate<br>Wall mounting blind-nuts  |
| Dimensions                           | Width: 500 mm<br>Height: 600 mm<br>Depth: 210 mm<br>Width: 19.7 "<br>Height: 23.6 "<br>Depth: 8.27 "   |
| Dimensions of mounting plate (W x H) | 449 mm x 570 mm<br>17.7 " x 22.4 "   |
| Protection category NEMA             | NEMA 4X  |
| Material thickness - door            | 1.5 mm<br>0.06 "   |
| Material thickness - enclosure       | 1.5 mm<br>0.06 "   |
| Material thickness – mounting plate  | 2.5 mm<br>0.1 "  |

# Features

---

|                       |                            |
|-----------------------|----------------------------|
| Lock                  | Lock version: Quarter turn |
| Packaging unit        | 1 pc(s).                   |
| Gross weight          | 42.95 lb                   |
| Customs tariff number | 8538100000                 |

---

# Approvals

---

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Explanations | Declaration of conformity |

---