
RITTAL

# WM 8017.605 - WM wall-mounted enclosure 304 stainless steel

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a stainless steel body and door, and a zinc plated mounting panel.

## Features

| | |
|---|---|
| Model No. | WM 8017.605 |
| Material | Door: Stainless steel, all-round foamed-in PU seal<br>Housing and door: Stainless steel 1.4301 (AISI 304)<br>Mounting plate: Carbon steel, zinc-plated |
| Surface finish | Brushed |
| Supply includes | Housing with door(s)<br>Door hinged on left<br>Mounting plate<br>Wall mounting blind-nuts |
| Dimensions | Width: 400 mm<br>Height: 500 mm<br>Depth: 210 mm<br>Width: 15.7 ″<br>Height: 19.7 ″<br>Depth: 8.27 ″ |
| Dimensions of mounting plate (W x H) | 354 mm x 475 mm<br>13.9 ″ x 18.7 ″ |
| Protection category NEMA | NEMA 4X |
| Material thickness - door | 1.5 mm<br>0.06 ″ |
| Material thickness - enclosure | 1.5 mm<br>0.06 ″ |
| Material thickness – mounting plate | 1.5 mm<br>0.06 ″ |

© Rittal 2026

# Features

| | |
|---|---|
| Lock | Lock version: Quarter turn |
| Packaging unit | 1 pc(s). |
| Net weight | 26.455 lb |
| Gross weight | 28.007 lb |
| Customs tariff number | 8538100000 |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Manufacturer's declaration<br>Declaration of conformity |