Rittal – The System.

Faster – better – everywhere.



WM 8017.608

WM wall-mounted enclosure


State: 11/13/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

WM 8017.608 - WM wall-mounted enclosure 304 stainless steel

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a stainless steel body and door, and a zinc plated mounting panel.



Features

Model No.	WM 8017.608
Material	Door: Stainless steel, all-round foamed-in PU seal Housing and door: Stainless steel 1.4301 (AISI 304) Mounting plate: Carbon steel, zinc-plated
Surface finish	Brushed
Supply includes	Housing with door(s) Door hinged on left Mounting plate Wall mounting blind-nuts
Dimensions	Width: 300 mm Height: 400 mm Depth: 210 mm Width: 11.8 ″ Height: 15.7 ″ Depth: 8.27 ″
Dimensions of mounting plate (W x H)	254 mm x 375 mm 10 ″ x 14.8 ″
Protection category NEMA	NEMA 4X

Features

Material thickness - door	1.5 mm 0.06 ″
Material thickness - enclosure	1.5 mm 0.06 ″
Material thickness – mounting plate	1.5 mm 0.06 ″
Lock	Lock version: Quarter turn
Packaging unit	1 pc(s).
Net weight	18.186 lb
Gross weight	21.561 lb
Customs tariff number	8538100000

Approvals

Approvals	UL + C-UL (listed)
Explanations	Manufacturer's declaration Declaration of conformity