### Rittal – The System.

Faster – better – everywhere.





# WM 8017.610 WM wall-mounted enclosure

State: 12/3/2025 (Source: rittal.com/us-en)



# WM 8017.610 - WM wall-mounted enclosure 304 stainless steel

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a stainless steel body and door, and a zinc plated mounting panel.

#### **Features**

Model No.	WM 8017.610
Material	Door: Stainless steel, all-round foamed-in PU seal
	Housing and door: Stainless steel 1.4301 (AISI 304)
	Mounting plate: Carbon steel, zinc-plated
Surface finish	Brushed
Supply includes	Housing with door(s)
	Door hinged on left
	Mounting plate
	Wall mounting blind-nuts
Dimensions	Width: 400 mm
	Height: 400 mm
	Depth: 150 mm
	Width: 15.7 "
	Height: 15.7 "
	Depth: 5.91 "
Dimensions of mounting plate (W	354 mm x 375 mm
x H)	13.9 ″ x 14.8 ″
Protection category NEMA	NEMA 4X
Material thickness - door	1.5 mm
	0.06 ″
Material thickness - enclosure	1.5 mm
	0.06 "
Material thickness – mounting	1.5 mm
plate	0.06 ″

© Rittal 2025

#### **Features**

Lock	Lock version: Quarter turn
Packaging unit	1 pc(s).
Net weight	19.841
Gross weight	20.944
Customs tariff number	7326908688
UPC-Code	83186

## **Approvals**

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3