

Rittal – The System.

Faster – better – everywhere.



WM 8017.615

WM wall-mounted enclosure

State: 6/11/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



WM 8017.615 - WM wall-mounted enclosure 304 stainless steel

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a stainless steel body and door, and a zinc plated mounting panel.

Features

| | |
|--------------------------------------|--|
| Model No. | WM 8017.615 |
| Material | Door: Stainless steel, all-round foamed-in PU seal Housing and door: Stainless steel 1.4301 (AISI 304) Mounting plate: Carbon steel, zinc-plated |
| Surface finish | Brushed |
| Supply includes | Housing with door(s) Door hinged on left Mounting plate Wall mounting blind-nuts |
| Dimensions | Width: 760 mm Height: 900 mm Depth: 210 mm Width: 29.9 " Height: 35.4 " Depth: 8.27 " |
| Dimensions of mounting plate (W x H) | 704 mm x 870 mm 27.7 " x 34.3 " |
| Protection category NEMA | NEMA 4X |
| Material thickness - door | 2 mm 0.08 " |
| Material thickness - enclosure | 2 mm 0.08 " |
| Material thickness – mounting plate | 2.5 mm 0.1 " |

Features

| | |
|-----------------------|----------------------------|
| Lock | Lock version: Quarter turn |
| Packaging unit | 1 pc(s). |
| Gross weight | 102 lb |
| Customs tariff number | 8538100000 |

Approvals

| | |
|--------------|---------------------------|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |
