Rittal – The System.

Faster – better – everywhere.





WM 8017.615 WM wall-mounted enclosure

State: 11/30/2025 (Source: rittal.com/us-en)



WM 8017.615 - WM wall-mounted enclosure 304 stainless steel

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a stainless steel body and door, and a zinc plated mounting panel.

Features

Model No.	WM 8017.615
Material	Door: Stainless steel, all-round foamed-in PU seal
	Housing and door: Stainless steel 1.4301 (AISI 304)
	Mounting plate: Carbon steel, zinc-plated
Surface finish	Brushed
Supply includes	Housing with door(s)
	Door hinged on left
	Mounting plate
	Wall mounting blind-nuts
Dimensions	Width: 760 mm
	Height: 900 mm
	Depth: 210 mm
	Width: 29.9 "
	Height: 35.4 "
	Depth: 8.27 "
Dimensions of mounting plate (W x H)	704 mm x 870 mm
	27.7 ″ x 34.3 ″
Protection category NEMA	NEMA 4X
Material thickness - door	2 mm
	0.08 ″
Material thickness - enclosure	2 mm
	0.08 "
Material thickness – mounting	2.5 mm
plate	0.1 ″

© Rittal 2025

Features

Lock	Lock version: Quarter turn
Packaging unit	1 pc(s).
Gross weight	102
Customs tariff number	7326908688
UPC-Code	83191

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3