

# Rittal – The System.

Faster – better – everywhere.



## WM 8017.617

## WM wall-mounted enclosure

State: 4/25/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# WM 8017.617 - WM wall-mounted enclosure 304 stainless steel

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a stainless steel body and door, and a zinc plated mounting panel.

## Features

Model No.	WM 8017.617
Material	Door: Stainless steel, all-round foamed-in PU seal Housing and door: Stainless steel 1.4301 (AISI 304) Mounting plate: Carbon steel, zinc-plated
Surface finish	Brushed
Supply includes	Housing with door(s) Door hinged on left Mounting plate Wall mounting blind-nuts
Dimensions	Width: 900 mm Height: 1,050 mm Depth: 300 mm Width: 35.4 " Height: 41.3 " Depth: 11.8 "
Dimensions of mounting plate (W x H)	840 mm x 1,020 mm 33.1 " x 40.2 "
Protection category NEMA	NEMA 4X
Material thickness - door	2 mm 0.08 "
Material thickness - enclosure	2 mm 0.08 "
Material thickness – mounting plate	2.5 mm 0.1 "

# Features

---

Lock	Lock version: 3-point locking system
Packaging unit	1 pc(s).
Net weight	169.753 lb
Gross weight	170 lb
Customs tariff number	8538100000

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity