Rittal – The System.

Faster – better – everywhere.





WM 8017.624 WM wall-mounted enclosure

State: 11/3/2025 (Source: rittal.com/us-en)



WM 8017.624 - WM wall-mounted enclosure 316 stainless steel

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a stainless steel 316L body and door, and a zinc plated mounting panel.



Features

Model No.	WM 8017.624
Material	Door: Stainless steel, all-round foamed-in PU seal
	Stainless steel 1.4404 (AISI 316L)
	Mounting plate: Carbon steel, zinc-plated
Surface finish	Brushed
Supply includes	Housing with door(s)
	Door hinged on left
	Mounting plate
	Wall mounting blind-nuts
Dimensions	Width: 500 mm
	Height: 500 mm
	Depth: 210 mm
	Width: 19.7 "
	Height: 19.7 "
	Depth: 8.27 "
Dimensions of mounting plate (W	449 mm x 470 mm
x H)	17.7 ″ x 18.5 ″
Protection category NEMA	NEMA 4X

© Rittal 2025 2

Features

Packaging unit	1 pc(s).
Net weight	35.999
Gross weight	35.999
Customs tariff number	7326908688
UPC-Code	83200

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3