
Rittal – The System.

Faster – better – everywhere.



WM 8017.626

WM wall-mounted enclosure

State: 10/31/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

WM 8017.626 - WM wall-mounted enclosure 316 stainless steel

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a stainless steel 316L body and door, and a zinc plated mounting panel.



Features

Model No.	WM 8017.626
Material	Door: Stainless steel, all-round foamed-in PU seal Stainless steel 1.4404 (AISI 316L) Mounting plate: Carbon steel, zinc-plated
Surface finish	Brushed
Supply includes	Housing with door(s) Door hinged on left Mounting plate Wall mounting blind-nuts
Dimensions	Width: 900 mm Height: 1,200 mm Depth: 300 mm Width: 35.4 ″ Height: 47.2 ″ Depth: 11.8 ″
Dimensions of mounting plate (W x H)	840 mm x 1,155 mm 33.1 ″ x 45.5 ″
Protection category NEMA	NEMA 4X

Features

Packaging unit	1 pc(s).
Net weight	189.594 lb
Gross weight	190 lb
Customs tariff number	8538100000

Approvals

Explanations	Declaration of conformity