Rittal – The System.

Faster – better – everywhere.





WM 8017.631 WM wall-mounted enclosure

State: 10/31/2025 (Source: rittal.com/us-en)



WM 8017.631 - WM wall-mounted enclosure 316 stainless steel

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a stainless steel 316L body and door, and a zinc plated mounting panel.



Features

Model No.	WM 8017.631
Material	Door: Stainless steel, all-round foamed-in PU seal
	Stainless steel 1.4404 (AISI 316L)
	· · · · · · · · · · · · · · · · · · ·
	Mounting plate: Carbon steel, zinc-plated
Surface finish	Brushed
Supply includes	Housing with door(s)
	Door hinged on left
	Mounting plate
	Wall mounting blind-nuts
Dimensions	Width: 900 mm
	Height: 1,500 mm
	Depth: 300 mm
	Width: 35.4 "
	Height: 59.1 "
	Depth: 11.8 "
Dimensions of mounting plate (W	840 mm x 1,455 mm
x H)	33.1 ″ x 57.3 ″
Protection category NEMA	NEMA 4X

© Rittal 2025 2

Features

Packaging unit	1 pc(s).
Net weight	219.996
Gross weight	219.996
Customs tariff number	7326909099
UPC-Code	83207

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3