

Rittal – The System.

Faster – better – everywhere.



WM 8017.633

WM wall-mounted enclosure

State: 4/14/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



WM 8017.633 - WM wall-mounted enclosure 316 stainless steel

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a stainless steel 316L body and door, and a zinc plated mounting panel.



Features

| | |
|--------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------|
| Model No. | WM 8017.633 |
| Material | Door: Stainless steel, all-round foamed-in PU seal Stainless steel 1.4404 (AISI 316L) Mounting plate: Carbon steel, zinc-plated |
| Surface finish | Brushed |
| Supply includes | Housing with door(s) Door hinged on left Mounting plate Wall mounting blind-nuts |
| Dimensions | Width: 900 mm Height: 1,500 mm Depth: 400 mm Width: 35.4 " Height: 59.1 " Depth: 15.7 " |
| Dimensions of mounting plate (W x H) | 840 mm x 455 mm 33.1 " x 17.9 " |
| Protection category NEMA | NEMA 4X |

Features

| | |
|-----------------------|------------|
| Packaging unit | 1 pc(s). |
| Net weight | 246.914 lb |
| Gross weight | 247.5 lb |
| Customs tariff number | 8538100000 |

Approvals

| | |
|--------------|---------------------------|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |
