

# Rittal – The System.

Faster – better – everywhere.



## WM 8017.644

## WM wall-mounted enclosure

State: 7/10/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# WM 8017.644 - WM wall-mounted enclosure 316 stainless steel

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a stainless steel 316L body and door, and a zinc plated mounting panel.



## Features

Model No.	WM 8017.644
Material	Door: Stainless steel, all-round foamed-in PU seal Stainless steel 1.4404 (AISI 316L) Mounting plate: Carbon steel, zinc-plated
Surface finish	Brushed
Supply includes	Housing with door(s) Door hinged on left Mounting plate Wall mounting blind-nuts
Dimensions	Width: 300 mm Height: 400 mm Depth: 210 mm Width: 11.8 " Height: 15.7 " Depth: 8.27 "
Dimensions of mounting plate (W x H)	254 mm x 375 mm 10 " x 14.8 "
Protection category NEMA	NEMA 4X

# Features

---

Packaging unit	1 pc(s).
Net weight	19.4 lb
Gross weight	19.996 lb
Customs tariff number	8538100000

---

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

---