Rittal – The System.

Faster – better – everywhere.



# PB 8017.667

# Pushbutton boxes PB

State: 11/19/2026 (Source: www.rittal.com/us-en)

# PB 8017.667 - Pushbutton boxes PB

## Features

| | |
|---|---|
| Model No. | PB 8017.667 |
| Material | Carbon steel |
| Surface finish | Housing and cover: Dipcoat primed, powder-coated on the outside, textured paint |
| Color | RAL 7035 |
| Supply includes | Cover screws, captive<br>Wall Mounting Brackets |
| Hole diameter | 22.5 mm |
| Number of holes | 4 |
| Number of columns | 1 |
| Number of rows | 4 |
| Dimensions | Width: 69 mm<br>Height: 225 mm<br>Depth: 88 mm<br>Width: 2.72 ″<br>Height: 8.86 ″<br>Depth: 3.46 ″ |
| Protection category NEMA | NEMA 12<br>NEMA 13<br>NEMA 4 |
| Packaging unit | 1 pc(s). |
| Net weight | 3.968 lb |
| Gross weight | 3.999 lb |
| Customs tariff number | 8538100000 |
| Product description | PB pushbutton box, 4-hole, 22.5 mm hole diameter, 8.86" H x 2.72" W x 3.46" D, Carbon Steel, Light Gray |

© Rittal 2026

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed) |