Rittal – The System.

Faster – better – everywhere.



# PB 8017.685

# Pushbutton boxes PB

State: 10/31/2026 (Source: www.rittal.com/us-en)


ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# PB 8017.685 - Pushbutton boxes PB extra deep

The NEMA rated PB series pushbutton box enclosure is designed for indoor and outdoor use to house pushbuttons, selector switches, and pilot lights. This enclosure protects equipment from dirt, dust, sprayed water, oil, and coolants.





## Features

| | |
|---|---|
| Model No. | PB 8017.685 |
| Material | Carbon steel |
| Surface finish | Housing and cover: Dipcoat primed, powder-coated on the outside, textured paint |
| Color | RAL 7035 |
| Supply includes | Wall mounting bracket<br>Mounting panel: Zinc-plated<br>Cover screws, captive |
| Hole diameter | 30.5 mm |
| Number of holes | 1 |
| Number of columns | 1 |
| Number of rows | 1 |

© Rittal 2026

# Features

| | |
|---|---|
| Dimensions | Width: 101 mm<br>Height: 101 mm<br>Depth: 120 mm<br>Width: 3.98 ″<br>Height: 3.98 ″<br>Depth: 4.72 ″ |
| Protection category NEMA | NEMA 12<br>NEMA 13<br>NEMA 4 |
| Packaging unit | 1 pc(s). |
| Net weight | 3 lb |
| Gross weight | 3.086 lb |
| Customs tariff number | 8538100000 |
| Product description | PB pushbutton box, extra deep, 1-hole, 30.5 mm hole diameter, 3.98" H x 3.98" W x 4.72" D, Carbon Steel, Light Gray |

# Approvals

| | |
|---|---|
| Approvals | UL + C-UL (listed) |