Rittal – The System.

Faster – better – everywhere.



PB 8017.727

Pushbutton boxes PB

State: 11/3/2026 (Source: www.rittal.com/us-en)

PB 8017.727 - Pushbutton boxes PB Stainless steel

The NEMA rated PB series pushbutton box enclosure is designed for indoor and outdoor use to house pushbuttons, selector switches, and pilot lights. This enclosure protects equipment from dirt, dust, sprayed water, oil, and coolants.

Features

Model No.	PB 8017.727
Material	Stainless steel 1.4301 (AISI 304)
Surface finish	Housing and cover: Brushed, grain 240
Supply includes	Wall mounting bracket Cover screws, captive
Hole diameter	22.5 mm
Number of holes	3
Number of columns	1
Number of rows	3
Dimensions	Width: 69 mm Height: 177 mm Depth: 88 mm Width: 2.72 ″ Height: 6.97 ″ Depth: 3.46 ″
Protection category NEMA	NEMA 12 NEMA 13 NEMA 4X
Packaging unit	1 pc(s).
Net weight	3 lb
Gross weight	3.086 lb
Customs tariff number	8538100000
Product description	PB pushbutton box, 3-hole, 22.5 mm hole diameter, 6.97" H x 2.72" W x 3.46" D, Stainless Steel

© Rittal 2026

Approvals

Approvals	UL + C-UL (listed)