Rittal – The System.

Faster – better – everywhere.



PB 8017.737

Pushbutton boxes PB

State: 11/20/2026 (Source: www.rittal.com/us-en)

PB 8017.737 - Pushbutton boxes PB extra deep stainless steel

The NEMA rated PB series pushbutton box enclosure is designed for indoor and outdoor use to house pushbuttons, selector switches, and pilot lights. This enclosure protects equipment from dirt, dust, sprayed water, oil, and coolants.

Features

Model No.	PB 8017.737
Material	Stainless steel 1.4301 (AISI 304)
Surface finish	Housing and cover: Brushed, grain 240
Supply includes	Wall Mounting Brackets Cover screws, captive
Hole diameter	30.5 mm
Number of holes	6
Number of columns	2
Number of rows	3
Dimensions	Width: 158 mm Height: 241 mm Depth: 120 mm Width: 6.22 ″ Height: 9.49 ″ Depth: 4.72 ″
Protection category NEMA	NEMA 12 NEMA 13 NEMA 4X
Packaging unit	1 pc(s).
Net weight	5.952 lb
Gross weight	6.001 lb
Customs tariff number	8538100000

Approvals

Approvals	UL + C-UL (listed)