Rittal – The System.

Faster – better – everywhere.





JB 8018.143 JB Junction box

State: 11/6/2025 (Source: rittal.com/us-en)



JB 8018.143 - JB Junction box 316 stainless steel

The JB enclosure offers protection for dense wiring and sensitive small instruments. These hinged cover junction boxes combine the advantages of the AE and KL series at an economical cost. Features include 180 degree hinge and slotted insert quarter turn latch. Foamed-in-place gasket and a knife-edge perimeter add extra protection. Stainless steel 1.4404 (AISI 316L).



Features

Model No.	JB 8018.143
Material	Stainless steel 1.4404 (AISI 316L)
Surface finish	Housing and door: Brushed, grain 240
Supply includes	180° hinge Mounting panel
Material thickness - door	1.5 mm 0.06 "
Material thickness - enclosure	1.5 mm 0.06 "
Position door catch	left
Dimensions	Width: 150 mm Height: 200 mm Depth: 100 mm Width: 5.91 " Height: 7.87 " Depth: 3.94 "
Protection category IP to IEC 60 529	IP 66
Protection category NEMA	NEMA 4X

© Rittal 2025 2

Features

Packaging unit	1 pc(s).
Net weight	4.189
Gross weight	4.2
Customs tariff number	7326909099
UPC-Code	83295

Approvals

Approvals UL + C-UL (listed)

© Rittal 2025 3