
Rittal – The System.

Faster – better – everywhere.



WK 8018.460
Window Kits

State: 11/5/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

WK 8018.460 - Window Kits Stainless steel

Features

Model No.	WK 8018.460
Material	Frame: Stainless steel 1.4301 (AISI 304) Viewing window: Polycarbonate
Surface finish	Brushed
Supply includes	Oil resistant gasket Fasteners
Visible area	Viewing window width: 279 mm Viewing window height: 432 mm Viewing window width: 11 ″ Viewing window height: 17 ″
Viewing window height	432 mm 17 ″
Dimensions	Width: 343 mm Height: 495 mm Width: 13.5 ″ Height: 19.5 ″
Packaging unit	1 pc(s).
Net weight	5.071 lb
Gross weight	5.071 lb
Customs tariff number	7326909099

Approvals

Approvals	UL + C-UL (listed)

© Rittal 2026