

Rittal – The System.

Faster – better – everywhere.



TS 8018.799

TS 8 Floormount Enclosure

State: 4/27/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8018.799 - TS 8 Floormount Enclosure

Rittal's Floormount TS 8 combines the strength of unibody floormount enclosures with the flexibility of Rittal's revolutionary modular design. With its double door configuration and wide range of accessories, Rittal's Floormount TS 8 is sure to meet your UL Type 12 needs.

Features

Model No.	TS 8018.799
Material	Enclosure frame: Carbon steel, 1.5 mm Roof: Carbon steel, 1.5 mm Door: Carbon steel, 2.0 mm Rear wall: carbon steel, 1.5 mm Mounting panel: Carbon steel, 3.0 mm
Surface finish	Enclosure frame: Dipcoat-primed Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Mounting plate and base plates: Zinc-plated
Color	RAL 7035
Supply includes	Enclosure frame with door(s) Roof plate Rear panel, detachable 4 eyebolts Padlock Comfort handle Base Plates Mounting plate 12 inch removable floor stands
Dimensions	Width: 1,200 mm Height: 1,600 mm Depth: 400 mm Width: 47.2 " Height: 63 " Depth: 15.7 "
Packaging unit	1 pc(s).
Net weight	358.999 lb
Gross weight	359.347 lb

Features

Customs tariff number 7326908688

Approvals

Approvals UL + C-UL (listed)