

Rittal – The System.

Faster – better – everywhere.



TS 8018.811

**TS 8 Flange Mount Disconnect
Floormount Enclosure**

State: 10/3/2025 (Source: [rittal.com/us-en](https://www.rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8018.811 - TS 8 Flange Mount Disconnect Floormount Enclosure

Rittal's Floormount TS 8 combines the strength of unibody floormount enclosures with the flexibility of Rittal's revolutionary modular design. With its double door configuration and wide range of accessories, Rittal's Floormount TS 8 is sure to meet your UL Type 12 needs.

Features

Model No.	TS 8018.811
Product description	Rittal's Floormount TS 8 combines the strength of unibody floormount enclosures with the flexibility of Rittal's revolutionary modular design. With its double door configuration and wide range of accessories, Rittal's Floormount TS 8 is sure to meet your UL Type 12 needs. Includes operator handle interlocking kit to securely lock most commercially available operator handles to enclosure and door latch.
Material	Enclosure frame: Carbon steel, 1.5 mm Roof: Carbon steel, 1.5 mm Door: Carbon steel, 2.0 mm Rear wall: carbon steel, 1.5 mm Mounting panel: Carbon steel, 3.0 mm
Color	RAL 7035
Supply includes	Enclosure frame with door(s) Roof plate Rear panel, detachable 4 eyebolts
Dimensions	Width: 1,800 mm Height: 1,800 mm Depth: 400 mm Width: 70.9 " Height: 70.9 " Depth: 15.7 "
Packaging unit	1 pc(s).
Gross weight	246.001

Features

Customs tariff number	7326909099
UPC-Code	85554

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------