

Rittal – The System.

Faster – better – everywhere.



WM 8018.904

WM wall-mounted enclosure

State: 4/2/2026 (Source: rittal.com/us-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



WM 8018.904 - WM wall-mounted enclosure 316 stainless steel

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a stainless steel 316L body and door, and a zinc plated mounting panel.



Features

Model No.	WM 8018.904
Material	Door: Stainless steel, all-round foamed-in PU seal Stainless steel 1.4404 (AISI 316L) Mounting plate: Carbon steel, zinc-plated
Surface finish	Brushed
Supply includes	Housing with door(s) Door hinged on left Mounting plate Wall mounting blind-nuts
Dimensions	Width: 760 mm Height: 760 mm Depth: 250 mm Width: 29.9 " Height: 29.9 " Depth: 9.84 "
Dimensions of mounting plate (W x H)	704 mm x 730 mm 27.7 " x 28.7 "
Protection category NEMA	NEMA 4X

Features

Packaging unit	1 pc(s).
Net weight	84.998 lb
Gross weight	84.998 lb
Customs tariff number	7326909099

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity