Rittal – The System.

Faster – better – everywhere.





WM 8018.963 WM wall-mounted enclosure

State: 12/12/2025 (Source: rittal.com/us-en)



WM 8018.963 - WM wall-mounted enclosure single-door

These single door wallmount enclosures can be used for virtually any application. The WM series ensures NEMA protection through a secure locking system, foamed-in-place gasket, and knife-edge sealing surface. Features include a cold rolled steel body and door, and a zinc plated mounting panel.







Features

Model No.	WM 8018.963
Material	Door: Carbon steel, all-round foamed-in PU seal Housing: Carbon steel
	Housing. Carbon steel
Surface finish	Housing and door: Dipcoat primed, powder-coated on the outside,
	textured paint
	Mounting panel: Zinc-plated
Color	RAL 7035
Supply includes	Housing with door(s)
	Door hinged on left
	Mounting plate
	Rear wall mounting holes
	Quarter turn latch with slotted head insert
Dimensions	Width: 500 mm
	Height: 500 mm
	Depth: 250 mm
	Width: 19.7 "
	Height: 19.7 ″
	Depth: 9.84 "
Dimensions of mounting plate (W	449 mm x 475 mm
x H)	17.7 ″ x 18.7 ″

© Rittal 2025 2

Features

Protection category NEMA	NEMA 1
	NEMA 3R
	NEMA 4
	NEMA 12
Material thickness - door	1.5 mm
	0.06 ″
Material thickness - enclosure	1.5 mm
	0.06 ″
Material thickness – mounting	2.5 mm
plate	0.1 "
Packaging unit	1 pc(s).
Net weight	38.6
Gross weight	39.01
Customs tariff number	7326909099
UPC-Code	85563

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

© Rittal 2025 3