


# Rittal – The System.

Faster – better – everywhere.



## TS 8018.965

## TS 8 Floormount Enclosure

State: 9/17/2025 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8018.965 - TS 8 Floormount Enclosure Type 3R

The Type 3R rated TS8 floormount enclosure includes all the features and benefits of Rittal's TS8 enclosure line – with the addition of a unique roof design that shrouds the top of the enclosure to prevent the entry of water. The floormount enclosure sits atop 12-inch legs which ensure that water accumulation on the floor cannot enter the enclosure.

## Features

|                          |   |
|--------------------------|---|
| Model No.                | TS 8018.965   |
| Material                 | Enclosure frame: Carbon steel, 1.5 mm<br>Roof: Carbon steel, 1.5 mm<br>Door: Carbon steel, 2.0 mm<br>Rear wall: carbon steel, 1.5 mm<br>Mounting panel: Carbon steel, 3.0 mm    |
| Surface finish           | Enclosure frame: powder-coated<br>Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint<br>Mounting panel: Zinc-plated                        |
| General color            | RAL 7035  |
| Color                    | RAL 7035  |
| Supply includes          | Enclosure frame with door(s)<br>Roof plate<br>Rear panel, detachable<br>4 eyebolts<br>Padlock Comfort handle<br>Base Plates<br>Mounting plate<br>12 inch removable floor stands |
| Dimensions               | Width: 1,200 mm<br>Height: 1,600 mm<br>Depth: 500 mm<br>Width: 47.2 "<br>Height: 63 "<br>Depth: 19.7 "  |
| Protection category NEMA | UL Type 3R  |

# Features

|                       |            |
|-----------------------|------------|
| Packaging unit        | 1 pc(s).   |
| Gross weight          | 541.001    |
| Customs tariff number | 7326909099 |
| UPC-Code              | 85565      |

# Approvals

|           |                    |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|