Rittal – The System.

Faster – better – everywhere.



TS 8018.965

TS 8 Floormount Enclosure

State: 11/1/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

TS 8018.965 - TS 8 Floormount Enclosure Type 3R

The Type 3R rated TS8 floormount enclosure includes all the features and benefits of Rittal's TS8 enclosure line — with the addition of a unique roof design that shrouds the top of the enclosure to prevent the entry of water. The floormount enclosure sits atop 12-inch legs which ensure that water accumulation on the floor cannot enter the enclosure.

Features

Model No.	TS 8018.965
Material	Enclosure frame: Carbon steel, 1.5 mm Roof: Carbon steel, 1.5 mm Door: Carbon steel, 2.0 mm Rear wall: carbon steel, 1.5 mm Mounting panel: Carbon steel, 3.0 mm
Surface finish	Enclosure frame: powder-coated Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Mounting panel: Zinc-plated
General color	RAL 7035
Color	RAL 7035
Supply includes	Enclosure frame with door(s) Roof plate Rear panel, detachable 4 eyebolts Padlock Comfort handle Base Plates Mounting plate 12 inch removable floor stands
Dimensions	Width: 1,200 mm Height: 1,600 mm Depth: 500 mm Width: 47.2 ˝ Height: 63 ˝ Depth: 19.7 ˝
Protection category NEMA	UL Type 3R

© Rittal 2026

Features

Packaging unit	1 pc(s).
Gross weight	541.001 lb
Customs tariff number	7326909099

Approvals

Approvals	UL + C-UL (listed)