## Rittal – The System.

Faster – better – everywhere.





# TS 8018.972 TS 8 Floormount Enclosure

State: 11/6/2025 (Source: rittal.com/us-en)



## TS 8018.972 - TS 8 Floormount Enclosure Type 3R

The Type 3R rated TS8 floormount enclosure includes all the features and benefits of Rittal's TS8 enclosure line — with the addition of a unique roof design that shrouds the top of the enclosure to prevent the entry of water. The floormount enclosure sits atop 12-inch legs which ensure that water accumulation on the floor cannot enter the enclosure.

#### **Features**

Model No.	TS 8018.972
Material	Enclosure frame: Carbon steel, 1.5 mm
	Roof: Carbon steel, 1.5 mm
	Door: Carbon steel, 2.0 mm
	Rear wall: carbon steel, 1.5 mm
	Mounting panel: Carbon steel, 3.0 mm
Surface finish	Enclosure frame: powder-coated
	Door, roof and rear panel: Dipcoat-primed, powder-coated on the
	outside, textured paint
	Mounting panel: Zinc-plated
General color	RAL 7035
Color	RAL 7035
Supply includes	Enclosure frame with door(s)
	Roof plate
	Rear panel, detachable
	4 eyebolts
	Padlock Comfort handle
	Base Plates
	Mounting plate
	12 inch removable floor stands
Dimensions	Width: 1,800 mm
	Height: 1,800 mm
	Depth: 600 mm
	Width: 70.9 "
	Height: 70.9 "
	Depth: 23.6 "
Protection category NEMA	UL Type 3R

© Rittal 2025

## Features

Packaging unit	1 pc(s).
Customs tariff number	7326909099
UPC-Code	85572

## **Approvals**

Approvals UL + C-UL (listed)

© Rittal 2025 3