

# Rittal – The System.

Faster – better – everywhere.



## TS 8026.548

## Baying systems TS 8

State: 5/13/2026 (Source: [rittal.com/us-en](http://rittal.com/us-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8026.548 - Baying systems TS 8 Type 3R

Rittal perfected the concept of the industrial modular enclosure with the TS 8 series. These single door, UL Type 3R rated enclosures consist of a frame with door, rear wall, and roof plate. Purchase sidewalls and plinth separately for complete assembly.

## Features

Model No.	TS 8026.548
Material	Enclosure frame: Carbon steel, 1.5 mm Roof: Carbon steel, 1.5 mm Door: Carbon steel, 2.0 mm Rear wall: carbon steel, 1.5 mm Mounting panel: Carbon steel, 3.0 mm
Surface finish	Enclosure frame: powder-coated Door, roof and rear panel: Dipcoat-primed, powder-coated on the outside, textured paint Mounting plate and base plates: Zinc-plated
Color	RAL 7035
Supply includes	Enclosure frame with door(s) Roof plate Rear panel, detachable 4 eyebolts Base Plates Mounting plate
Dimensions	Width: 1,000 mm Height: 2,200 mm Depth: 600 mm Width: 39.4 " Height: 86.6 " Depth: 23.6 "
Protection category NEMA	NEMA 3R
Packaging unit	1 pc(s).
Net weight	364.993 lb
Gross weight	364.993 lb

# Features

---

Customs tariff number                      9403200082

# Approvals

---

Approvals                                      UL + C-UL (listed)