Rittal – The System.

Faster – better – everywhere.





State: 11/25/2025 (Source: rittal.com/us-en)

RITTAL

TS 8106.235 - Side wall, screwable, carbon steel for TS, TS IT

Side panels, screw-fastened, sheet steel, for TS.

Features

Model No.	TS 8106.235
Benefits	Automatic potential equalization and higher EMC protection thanks to enclosure panel holders with grounding insert Easy positioning with the location aid Grounding bolt with contact surface
Material	Carbon steel, 1.5 mm
Surface finish	Dipcoat-primed, powder-coated on the outside
Color	RAL 7035
Supply includes	Assembly components
Note	Enclosure panel holders may optionally be fitted from the inside or outside of the enclosure. Area available for population: External dimension – 100 mm
Suitable for	Enclosure type: TS TS IT Height: 2,000 mm Depth: 600 mm Enclosure type: TS TS IT Height: 78.7 " Depth: 23.6 "
Protection category IP to IEC 60 529	IP 55
Base material	Carbon steel
Packaging unit	2 pc(s).
Net weight	28
Gross weight	29.2

© Rittal 2025

Features

Customs tariff number	94039910
EAN	4028177205260
E-Number Sweden	E7282533
ETIM 9	EC002524
ECLASS 8.0	27182101

Approvals

Explanations Declaration of conformity UK

© Rittal 2025 3