Rittal – The System.

Faster – better – everywhere.



# TS 8128.235

# Side wall, screwable, carbon steel

State: 10/31/2026 (Source: www.rittal.com/us-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# TS 8128.235 - Side wall, screwable, carbon steel for TS, TS IT

Side panels, screw-fastened, sheet steel, for TS.

## Features

| | |
|---|---|
| Model No. | TS 8128.235 |
| Benefits | Automatic potential equalization and higher EMC protection thanks to enclosure panel holders with grounding insert<br>Easy positioning with the location aid<br>Grounding bolt with contact surface |
| Material | Carbon steel, 1.5 mm |
| Surface finish | Dipcoat-primed, powder-coated on the outside |
| Color | RAL 7035 |
| Supply includes | Assembly components |
| Note | Enclosure panel holders may optionally be fitted from the inside or outside of the enclosure.<br>Area available for population: External dimension – 100 mm |
| Suitable for | Enclosure type: TS<br>TS IT<br>Height: 2,200 mm<br>Depth: 800 mm<br>Enclosure type: TS<br>TS IT<br>Height: 86.6 ″<br>Depth: 31.5 ″ |
| Protection category IP to IEC 60 529 | IP 55 |
| Base material | Carbon steel |
| Packaging unit | 2 pc(s). |
| Net weight | 43 kg |
| Gross weight | 44 kg |

© Rittal 2026

# Features

| | |
|---|---|
| Customs tariff number | 94039910 |
| ETIM 9 | EC002524 |
| ECLASS 8.0 | 27182101 |
| Product description | TS Side panel, screw-fastened, for TS, TS IT, for WD: 2200x800 mm, Sheet steel |