### Rittal – The System.

Faster – better – everywhere.





## TS 8175.235 Side wall, screwable, carbon steel

State: 10/29/2025 (Source: rittal.com/us-en)



# TS 8175.235 - Side wall, screwable, carbon steel for TS, TS IT

Side panels, screw-fastened, sheet steel, for TS.

#### **Features**

Model No.	TS 8175.235
Benefits	Automatic potential equalization and higher EMC protection thanks
	to enclosure panel holders with grounding insert
	Easy positioning with the location aid
	Grounding bolt with contact surface
Material	Carbon steel, 1.5 mm
Surface finish	Dipcoat-primed, powder-coated on the outside
Color	RAL 7035
Supply includes	Assembly components
Note	Enclosure panel holders may optionally be fitted from the inside or
	outside of the enclosure.
	Area available for population: External dimension – 100 mm
Suitable for	Enclosure type: TS
	TS IT
	Height: 1,200 mm
	Depth: 800 mm
	Enclosure type: TS
	TS IT
	Height: 47.2 "
	Depth: 31.5 "
Protection category IP to IEC 60 529	IP 55
Base material	Carbon steel
Packaging unit	2 pc(s).
Net weight	20
Gross weight	23.8

© Rittal 2025

### **Features**

Customs tariff number	94039910
EAN	4028177317529
E-Number Sweden	E7282543
ETIM 9	EC002524
ECLASS 8.0	27182101

© Rittal 2025 3